



**TRINITY TOOL
COMPANY**

*Leader in Blast Cleaning Since
1951*

*34600 Commerce Road
Fraser, Michigan 48026
PH: (586) 296-5900
FAX: (586) 296-5836*

**TRINCO™ MASTER MODEL 40 X 40 SPLIT LEVEL
WITH 600 CFM ABRASIVE SEPARATOR**

- Ruggedly built of 14 Gauge welded steel
- Double floor - 1/8" Expandex steel plus Carbon screen
- Trinco™ Tungsten carbide nozzle
- Trinco™ safety enclosed floor valve blasting control
- Trinco™ fluorescent lighting to eliminate shadows and minimize energy usage
- Trinco™ large 12"x24" safety glass window for excellent visibility and increased operator efficiency
- Air pressure regulator and gauge
- Trinco™ filter bag
- Trinco™ easy change window frames
- Trinco™ heavyweight Neoprene gloves



Inside

Depth	40"
Width	40"
Height	31"

Overall

Depth	66" Completely open 71"
Width	45"
Height	71"

Door Openings

Two (2)	
Flip Top	40" x 40"
Side Door	20" x 30"

Shipping Weight

Approximately 740 Lbs.

Optional Accessories:

- Water Filter
- Blow Off Gun
- Turntable
- Auto Power Basket
- Spare parts package
- Abrasives

Also available with Trinco™ Deluxe package or DP 850 Pressure package

TRINCO™ DRY BLAST APPLICATIONS

The applications of Trinco™ Cabinets are virtually limitless - cleaning, deburring, decorating, deflashing, etching, finishing, honing, peening, etc. All of these uses and more can be accomplished easily with quick sweeps of the gun nozzle. Scale corrosion, old paint and other surface materials are removed in minutes leaving metal surfaces free of foreign matter and contamination. Even tough mill scale is quickly and efficiently removed.

The usual operating pressure for the Trinco™ Dry Blast Cabinets is 85 PSI. The equipment utilizes a variety of abrasives such as Trin Mixes™, glass beads, aluminum oxide, silicon carbide, nut shells, etc. A multitude of finishes are possible ranging from a micro-finish to a coarse-grade finish depending upon the specific media used. Trinco™ Cabinets can apply the proper abrasive to provide the desired finish for each specific application.

Rev 4/02 - web:

www.trinco.com